
## **Copy counters**

## FLDK 110G1303/S14



general data	
measuring distance Sd	0 60 mm
optimum operating distance	40 mm
counting rate	< 600000 copies/h
object speed	< 5 m/sec
sensitivity	single sheet/edge thickness 0,2 mm
sync. input	no
measuring point	visible red laser line 2 mm
light source	pulsed red laser diode
wave length	670 nm
laser class	2
edge indicator	LED yellow
power on indication	LED green
false pulse suppression	on/off switchable

electrical data	
voltage supply range +Vs	10 30 VDC
current consumption max. (no load)	180 mA
output circuit	push-pull
output pulse length	5 / 10 ms selectable
short circuit protection	yes
reverse polarity protection	yes

mechanical data	
width / diameter	30 mm
type	rectangular
housing material	PA 6
connector base (main connector)	M12 x 1, 5 pin
front (optics)	glass

ambient conditions	
operating temperature	0 +50 °C
protection class	IP 54



