
## Through beam sensors

### OR18.TL-11157829




#### general data

general data	
type	through beam sensor
emitter / receiver	emitter
light source	pulsed red laser diode
actual range Sb	55 m
nominal range Sn	60 m
power on indication	LED green
emission power adjustment	no
laser class	1
distance to focus	parallel beam
wave length	630 nm
electrical data	
voltage supply range +Vs	10 30 VDC
current consumption max. (no load)	45 mA
current consumption typ.	35 mA
reverse polarity protection	yes
mechanical data	
width / diameter	18 mm
height / length	71,5 mm
type	cylindrical threaded
housing material	brass nickel plated
front (optics)	PMMA
connection types	connector M12 4 pin
ambient conditions	
operating temperature	-10 +55 °C
protection class	IP 67



#### connection diagram



# Laser warning

IEC 60825-1/2014 Complies with 21 CFR 1040.10 and 1040.11 except for deviations pursuant to laser notice No. 50, dated June 24, 2007

PRODUCT