ESG 32SH0500G

Shielded cable 3 wires, 5,0 m Article number: 10125607



features

- shielded power cable
- M8/3-pin female connector to open wires
- cable carrier compatible
- length 5,0 m

bending radius (static)	25 mm	
bending radius (moved installation)	50 mm	
bending cycles	4000000	
use in cable carriers yes		
cable length [m]	5 m	
weight	≤ 171 g	
material	PUR	

electrical data	
shielding	yes
number of poles	3
connectors	M8 female connector, screw lock open wires

interface		
data interface	process interface	
environmental conditions		
flame resistance	DIN UL-Style 20549	
halogen-free	DIN VDE 0472 part 815	
resistance to oil	DIN EN 60811-2-1	
operation temperature (static	-25 +80 °C	
protection class	IP 65/67 (camera side)	

pin assignment



M8	color	
1:	BN	
4:	BK	
3:	BU	

mechanical data