# Shielded cable 3 wires, 10,0 m

Article number: 11002561



#### features

- shielded power cable
- M8/3-pin female connector to open wires
- cable carrier compatible
- length 10,0 m

mec	nani	ıcai	da	ta

bending radius 46 mm
(moved installation)

use in cable carriers yes
cable length [m] 10 m

weight ≤ 345 g

material PUR

### electrical data

shielding yes
number of poles 3
connectors M8 female connector, screw lock
open wires

## interface

data interface process interface

## environmental conditions

flame resistance VDE0472 part 804/B
resistance to oil VDE 0472 part 803
operation -50 ... +80 °C
temperature (static)
protection class IP 67 (camera side)

#### pin assignment



M8	color
1:	BN
4:	ВК
3:	BU