



features

- Gigabit Ethernet interface cable
- for TXG-I7 cameras
- CAT6
- M12 (screw lock) to RJ45
- cable carrier compatible
- length 30,0 m

mechanical data

bending radius (static)	45 mm
bending cycles	1000000
use in cable carriers	yes
cable length [m]	30 m
weight	≤ 1950 g
material	PVC

electrical data

transfer category	CAT6
number of poles	8
connectors	M12 male connector, screw lock RJ45


interface

data interface	GigE
----------------	------

environmental conditions

flame resistance	UL20276 (80°C, 30V)
protection class	IP 68 (camera side)

pin assignment



M12	RJ45	M12	RJ45
6:	1	1:	5
4:	2	8:	6
5:	3	2:	7
7:	4	3:	8