



features

- process interface cable
- M8/8-pin female connector to open wires
- cable carrier compatible
- length 10,0 m

mechanical data

use in cable carriers yes

cable length [m] 10 m

weight ≤ 310 g

electrical data

shielding no

number of poles 8

connectors M8 female connector, screw lock
open wires

interface

data interface process interface

environmental conditions

operation -40 ... +90 °C

temperature (static)

pin assignment



M8	wire color	M8	wire color
1:	WH	5:	GY
2:	BN	6:	PK
3:	GN	7:	BU
4:	YE	8:	RD