



features

- USB 3.0 PCIe interface board (2 ports)
- USB 3.0 cable, 3,0 m
- process interface cable 5,0 m
- Mounting Adapter Type A (Front)
- Mounting Adapter Type B (Tripod)
- Software (Windows®, Linux®, Linux® ARM®) via Download
- camera not included

interface card

article number	11141165
name	USB3.0 2 Port PCIe Card (ZVA-PCIe_2x_external_USB_3.0)
features	<ul style="list-style-type: none"> ▪ 2 port USB 3.0 board ▪ chipset: Renesas PD720202 ▪ tested bandwidth 2950Mbit/s ▪ 1 lane PCIe plug board ▪ tested driver version: Renesas 3.0.23.0

cable

article number	11140628
name	cable USB 3.0 die-cast MicB (screw)/A, 3,0 m (KSG U2/KSGU6GV0300G)
features	<ul style="list-style-type: none"> ▪ USB 3.0 interface cable with screwable Micro-B connector to USB 3.0 type A connector with screw lock option ▪ both connectors with die-cast housing ▪ length 3,0 m

process interface cable

article number	11118810
name	shielded cable 8 wires, 5,0 m (Z-ESG 32FP0500G)
features	<ul style="list-style-type: none"> ▪ shielded cable ▪ M8 female connector ▪ 8-pin ▪ open wires at one side ▪ cable carrier compatible ▪ length 5,0 m

fixing

article number	11002638
name	Mounting Adapter Type A (Front)
features	<ul style="list-style-type: none"> ▪ easy front side camera mounting ▪ robust anodized surface ▪ stable lightweight metal design (aluminium, 18 g)
article number	11003060
name	Mounting Adapter Type B (Tripod)
features	<ul style="list-style-type: none"> ▪ easy camera mounting ▪ robust anodized surface ▪ stable lightweight metal design (aluminium, 17g) ▪ UNC 1/4"- 20 thread for mounting (tripod thread)