19/11/2018 Subject to modification in technic and design. Errors and omissions excepted.

Totalizers mechanic

Revolution counter Display 5-digits, reset button

U 126



U 126 - Revolution counter

Technical data - mechanical design	
Function	Revolution counter
Display	White numbers on black
Number of digits	5-digits
Digit height	4.5 mm
Zero setting	Reset by knurled knob
Count mode	Adding in a rotational direction to be indicated, subtracting in reverse direction. 1 rev. = 1 count
Drive shaft	Right or left, ø4 mm
Operating speed	≤2000 rpm
Measuring range	99 999
Ambient temperature	0+60 °C
Housing type	Surface mount housing with mounting plate
Housing colour	Grey
Dimensions W x H x L	40 x 29 x 27.5 mm
Dimensions mounting plate	e 60 x 29 mm
Mounting type	Base plate, 4 mounting holes
Weight approx.	90 g
Materials	Housing: Hostaform POM, grey Base blate: steel zinc-coated

Features


- Revolution counter
- Adding
- Display 5-digits
- Manual reset by knurled knob

Totalizers mechanic

Revolution counter Display 5-digits, reset button


U 126

Part number




Direction of strokes and rotation

Drive on the right



Reset button left Away from user Direction of rotation or stroke direction I



Reset button left Toward user Direction of rotation or stroke direction II

Drive on the left



Reset button right way from user Direction of rotation or stroke direction I

2



Reset button right Toward user Direction of rotation or stroke direction II

Reset button always opposite of drive.

Dimensions

