19/11/2018 Subject to modification in technic and design. Errors and omissions excepted.

Totalizers mechanic

Meter counter Display 6-digits, reset by key

M 300



M 300 - Meter counter

| Technical data - mechanical design | |
|------------------------------------|---|
| Function | Meter counter |
| Display | White numbers on black Decimal digits in red |
| Number of digits | 6-digits |
| Digit height | 4.5 mm |
| Zero setting | Key reset by detachable key either at left or right shaft. |
| Count mode | Adding in a rotational direction to be indicated, subtracting in reverse direction. 5 revs. = 10 counts |
| Drive shaft | Both sides, ø4 mm |
| Measuring speed | <100 m/min (measuring wheel) |
| Measuring accuracy | 1 dm |
| Measuring range | 99 999.9 m |
| Ambient temperature | 0+60 °C |
| Housing type | Surface mount housing with mounting plate |
| Housing colour | Grey |
| Dimensions W x H x L | 69 x 48 x 28 mm |
| Dimensions mounting plate | e 60 x 70 mm |
| Mounting type | Base plate, 6 long mounting holes |
| Weight approx. | 130 g |
| Materials | Housing: Hostaform POM, grey Base blate: steel zinc-coated |

Features


- Meter counter
- Adding
- Display 6-digits
- Reset by key

Totalizers mechanic

Meter counter

Display 6-digits, reset by key

M 300




Accessories

Measuring wheels

MR211.04A Circumf. 20 cm, knurled aluminium
MR241.04D Circumf. 20 cm, smooth Hytrel TPE-E
MR261.04A Circumf. 20 cm, knopped rubber NBR Nitril
MR291.04D Circumf. 20 cm, grooved Hytrel TPE-E

Direction of strokes and rotation








Toward user Direction of rotation or stroke direction II

Dimensions



Reset shaft for detachable key

