# 26/11/2018 Subject to modification in technic and design. Errors and omissions excepted.

# Preset counters mechanic

Revolution counter, subtracting
Display 4-digits, manual reset by button

### **UE102**



UE102 - Revolution counter

### **Features**

- Preset counter with one preset
- Revolution counter
- Subtracting
- Display 4-digits
- With reset button
- Surface mount housing

Technical data - electrical ratings	
Preset	1 preset
Preset setting	Press reset button and hold. Enter desired value in any order. Release reset button.
Trigger / end contact	At 0000: As momentary contact: Contact duration dependent on speed e.g. 100 ms, at 10000 rpm and 50 revolutions = 1 digit At 9999: As permanent contact, contact remains until reset. If no reset takes place, the contact switches back at 8999.
Trigger / precontact	Preset number as momentary contact. End contact as permanent contact
Output contact	Change-over contact
Switching voltage	230 VAC / VDC
Switching current	2 A
Switching capacity	100 VA / 30 W
Spark extinguisher	Recommended for inductive load

Technical data - mechanical design	
Function	Revolution counter with preset
Display	White numbers on black
Number of digits	4-digits
Digit height	5.5 mm
Count mode	Subtracting in a rotational direction to be indicated, adding in reverse direction
Drive shaft	Both sides, ø4 mm
Reset	Manual by button to preset
Operating speed	≤10000 rpm
Operating torque	≤0.8 Nm (with 1 rev. = 1 count) ≤0.4 Nm (with 50 rev. = 1 count)
Measuring range	See part number
Ambient temperature	0+60 °C
Housing type	Surface mount housing
Housing colour	Grey
Dimensions W x H x L	60 x 62 x 68.5 mm
Dimensions mounting plate	60 x 62 mm 60 x 85 mm
Mounting type	Surface mount housing
Weight approx.	350 g
Material	Housing: Hostaform POM, grey
Connection	Cable 0.3 m, 3-pin Cable 1 m, 3-pin

## **Preset counters mechanic**

# Revolution counter, subtracting Display 4-digits, manual reset by button

### **UE102**

### Part number Connection diagram UE102.0 0 braun & grau (blau) Measuring range / trigger brown schwarz gray (blue) 9999 m / Contact at 0000 black 8999 m / Contact at 9999 The connection diagram illustrates the 8999 m / Contact at ready status (counter preselected). 9999, with precontact Direction of strokes and rotation Count mode /Direction of rotation 05 1 rev. = 10 digits / I 06 1 rev. = 10 digits / II 11 1 rev. = 1 digit / I Away from user Towards user 12 1 rev. = 1 digit / II Direction of rotation I Direction of rotation II Housing A Grey, cable 0.3 m / without precontact / mounting plate 60 x 62 mm E Grey, cable 1.0 m / with precontact / mounting plate 60 x 62 mm C Grey, cable 0.3 m / without precontact / mounting plate 60 x 85 mm Trigger Momentary contact at 0000 2 Permanent contact at 9999

Permanent contact at 9999, permanent precontact (\*) as momentary contact (\*) indicate desired value when ordering


# Preset counters mechanic


Revolution counter, subtracting Display 4-digits, manual reset by button

### **UE102**


### **Dimensions**

### **UE102**






### Mounting plate 60 x 62 mm



### Mounting plate 60 x 85 mm



3