

ZVI-RONDOLX_24VDC_WEIß_120°

RONDO-LX white 120° 24VDC with M8 connector

Article number: 11130179

overview

- flashable LED ring light
- white
- radiation angle 120°
- 24 V
- M8/4-pin connector (cable has to be ordered separately)
- diameter: 101 mm



technical data

general data

manufacturer Büchner Lichtsysteme GmbH

illumination data

color white

electrical data

number of poles 4
illumination connector • M8 connector
current 0,3 A
current at flash mode ≤ 0,45 A
voltage at flash mode ≤ 48 V DC
duty cycle 0-10%

electrical data

maximum flash duration 1 ms


mechanical data

construction design ring light
dimensions Ø 101 mm
dimensions luminous area Ø external 101 mm Ø internal 67 mm
material of cover glass acrylic
weight ≤ 160 g
material aluminum (anodized)

environmental conditions

operating temperature max. 50 °C

dimension drawing




ZVI-RONDOLX_24VDC_WEIß_120°

RONDO-LX white 120° 24VDC with M8 connector

Article number: 11130179

pin assignment



M8	signal
1:	LED +24V (pulsing 24-48 V)
2:	N.C.
3:	LED - (GND)
4:	N.C.