

Obj Kowa LM8JC10M 8,5mm/1,8

Article number: 11091819

overview

- Kowa lens
- 8,5 mm
- F 1,6-22
- format 2/3"
- M.O.D. 0,1 m
- locating screw for aperture and focus
- C-mount



technical data

general data

manufacturer Kowa

mechanical data

lens mount C-mount

dimensions 36 mm × 56 mm

max. outer diameter 36 mm (without knurled screws)
46 mm (with knurled screws)

max. length (excl. thread) 56 mm

weight ≤ 115 g

filter thread M 34,0 × 0,5

lens data

lens resolution 9 MP

focal length 8,5 mm

lens data

focal range < 12 mm

format 2/3"

aperture F1,8-22

aperture control manual

M.O.D. 0,1 m

horizontal angle of view 54 °

vertical angle of view 41,9 °

diagonal angle of view 64,6 °

at image format 6,6 × 8,8 mm

environmental conditions

operating temperature -10 ... +50 °C