

Obj Cinegon 2,1/6-0901

Article number: 11051937

overview

- Schneider Kreuznach lens
- 6 mm
- F 2,1-16
- format 2/3"
- M.O.D. 0,05 m
- C-mount



technical data

general data

manufacturer Schneider Kreuznach

mechanical data

lens mount C-mount

dimensions 34 mm × 49,5 mm

max. outer diameter 34 mm (without knurled screws)
44 mm (with knurled screws)

max. length (excl. thread) 40,9 mm

weight ≤ 154 g

filter thread M62 x 0.75

lens data

lens resolution 5 MP

focal length 6 mm

focal range < 12 mm

format 2/3"

aperture F2,1-16

aperture control manual

M.O.D. 0,05 m

environmental conditions

storage temperature -25 ... +70 °C