

Obj Cinegon 1,9/10-0901

Article number: 11037743

overview

- Schneider Kreuznach lens
- 10 mm
- F 1,9-22
- format 1"
- M.O.D. 0,092 m
- C-mount



technical data

general data

manufacturer Schneider Kreuznach

mechanical data

lens mount C-mount

dimensions 37,3 mm × 50,2 mm

max. outer diameter 37,3 mm (without knurled screws)
47,3 mm (with knurled screws)

max. length (excl. thread) 46,1 mm

weight ≤ 180 g

lens data

lens resolution 5 MP

focal length 10 mm

focal range < 12 mm

format 1"

aperture F1,9-22

aperture control manual

M.O.D. 0,092 m

environmental conditions

storage temperature -25 ... +70 °C