

Obj Kowa LM50HC 50mm/f1,4

Article number: 11143331

overview

- Kowa lens
- 50 mm
- F 1,4-16
- format 1"
- M.O.D. 0,5 m
- C-mount



technical data

general data

manufacturer Kowa

mechanical data

lens mount C-mount

dimensions 49 mm × 54.4 mm

max. outer diameter 49 mm (without knurled screws)
57 mm (with knurled screws)

max. length (excl. thread) 54,4 mm

weight ≤ 210 g

filter thread M 40,5 × 0,5

lens data

lens resolution 7 MP

focal length 50 mm

lens data

focal range ≥ 50 mm

format 1"

aperture F1,4-16

aperture control manual

M.O.D. 0,5 m

horizontal angle of view 14,5 °

vertical angle of view 10,8 °

diagonal angle of view 18 °

at image format 12,8 × 9,6 mm

environmental conditions

operating temperature -10 ... +50 °C