

Obj LINOS MeVis C 16mm/f1,6

Article number: 11051403

overview

- Linos lens
- 16 mm
- F 1,6-16
- format 2/3"
- M.O.D. 0,15 m
- C-mount



technical data

general data

manufacturer Linos

mechanical data

lens mount C-mount

dimensions 42 mm × 51,5 mm

max. outer diameter 42 mm (without knurled screws)
52 mm (with knurled screws)

max. length (excl. thread) 51,5 mm

weight ≤ 170 g

filter thread M 35,5 × 0,5

lens data

lens resolution 9 MP

focal length 16 mm

focal range ≥ 12 mm ... < 25 mm

format 2/3"

aperture F1,6-16

aperture control manual

M.O.D. 0,15 m