

Obj Xenoplan 1,4/23-0902

Article number: 11035165

overview

- Schneider Kreuznach lens
- 23 mm
- F 1,4-11
- format 2/3"
- M.O.D. 0,211 m
- C-mount



technical data

general data

manufacturer Schneider Kreuznach

mechanical data

lens mount C-mount

dimensions 34 mm × 40,4 mm

max. outer diameter 34 mm (without knurled screws)
44 mm (with knurled screws)

max. length (excl. thread) 40,4 mm

weight ≤ 95 g

filter thread M 30,5 × 0,5

lens data

lens resolution 5 MP

focal length 23 mm

focal range ≥ 12 mm ... < 25 mm

format 2/3"

aperture F1,4-11

aperture control manual

M.O.D. 0,211 m

environmental conditions

storage temperature -25 ... +70 °C