

## overview

- Carl Zeiss lens
- 35 mm
- F 2,0-22
- format 4/3"
- M.O.D. 0,209 m
- locating screw for aperture and focus
- C-mount



## technical data

### general data

manufacturer Carl Zeiss

### mechanical data

lens mount C-mount

dimensions 57 mm × 70 mm

max. outer diameter 57 mm (without knurled screws)  
70 mm (with knurled screws)

max. length (excl. thread) 70 mm

weight ≤ 323 g

filter thread M 49,0 × 0,75

### lens data

lens resolution 20 MP

focal length 35 mm

focal range ≥ 25 mm ... < 50 mm

format 4/3"

aperture F2,0-22

aperture control manual

M.O.D. 0,209 m

### environmental conditions

operating temperature -22 ... +55 °C