

ZVL-Dimension_2/50_C

Article number: 11214041

overview

- Carl Zeiss lens
- 50 mm
- F 2,0-22
- format 4/3"
- M.O.D. 0,311 m
- locating screw for aperture and focus
- C-mount



technical data

general data

manufacturer Carl Zeiss

mechanical data

lens mount C-mount

dimensions 57 mm × 69 mm

max. outer diameter 57 mm (without knurled screws)
64 mm (with knurled screws)

max. length (excl. thread) 81 mm

weight ≤ 306 g

filter thread M 49,0 × 0,75

lens data

lens resolution 20 MP

focal length 50 mm

focal range ≥ 50 mm

format 4/3"

aperture F2,0-22

aperture control manual

M.O.D. 0,311 m

environmental conditions

operating temperature -22 ... +55 °C