

overview

- Ricoh Imaging lens
- 12 mm
- F 2.0-16
- format 1,1"
- M.O.D. 0.08 m
- locating screw for aperture and focus
- C-mount



technical data

general data

manufacturer Ricoh Imaging

mechanical data

lens mount C-mount

dimensions 42 mm × 57,5 mm

max. outer diameter 42 mm (without knurled screws)
52 mm (with knurled screws)

max. length (excl. thread) 60,5 mm

weight ≤ 156 g

filter thread M 40,0 × 0,5

lens data

lens resolution 12 MP

focal length 12 mm

focal range ≥ 12 mm ... < 25 mm

format 1,1"

aperture F2.0-16

aperture control manual

M.O.D. 0,08 m