

ZVL-FL-BC2518-9M

Article number: 11154325

overview

- Ricoh Imaging lens
- 25 mm
- F 1,8-16
- format 1,1"
- M.O.D. 0,1 m
- locating screw for aperture and focus
- C-mount



technical data

general data

manufacturer Ricoh Imaging

mechanical data

lens mount C-mount

dimensions 42 mm × 57,5 mm

max. outer diameter 42 mm (without knurled screws)
52 mm (with knurled screws)

max. length (excl. thread) 57,5 mm

weight ≤ 149 g

filter thread M 40,0 × 0,5

lens data

lens resolution 12 MP

focal length 25 mm

focal range ≥ 25 mm ... < 50 mm

format 1,1"

aperture F1,8-16

aperture control manual

M.O.D. 0,1 m