

overview

- Computar lens
- 25 mm
- F 2,0-16
- format 1"
- M.O.D. 0,15 m
- locating screw for aperture and focus
- C-mount



technical data

general data

manufacturer Computar

mechanical data

lens mount C-mount

dimensions 37,5 mm × 44,04 mm

max. outer diameter 37,5 mm (without knurled screws)
47,5 mm (with knurled screws)

max. length (excl. thread) 44,6 mm

weight ≤ 73,1 g

filter thread M 35,5 × 0,5

lens data

lens resolution 20 MP

focal length 25 mm

lens data

focal range ≥ 25 mm ... < 50 mm

format 1"

aperture F2,0-16

aperture control manual

M.O.D. 0,15 m

horizontal angle of view 28,8 °

vertical angle of view 21,8 °

diagonal angle of view 35,5 °

at image format 12,8 × 9,6 mm

environmental conditions

operating temperature -10 ... +50 °C