

overview

- Computar lens
- 25 mm
- F 2,8-16
- format 1,1"
- M.O.D. 0,3 m
- locating screw for aperture and focus
- C-mount



technical data

general data

manufacturer Computar

mechanical data

lens mount C-mount

dimensions 39,5 mm × 34 mm

max. outer diameter 39,5 mm (without knurled screws)
49,5 mm (with knurled screws)

max. length (excl. thread) 37,7 mm

weight ≤ 79 g

filter thread M 34,0 × 0,5

lens data

lens resolution 12 MP

focal length 25 mm

lens data

focal range ≥ 25 mm ... < 50 mm

format 1,1"

aperture F2,8-16

aperture control manual

M.O.D. 0,3 m

horizontal angle of view 31,7 °

vertical angle of view 23,5 °

diagonal angle of view 38,7 °

at image format 16 × 12 mm

environmental conditions

operating temperature -10 ... +50 °C