

ZVL-LSF5028-U58

Article number: 11205386

overview

- Myutron lens
- 50 mm
- F 2,8-22
- format 44 mm
- M.O.D. 0,19 m
- locating screw for aperture and focus
- M58-mount
- focal flange distance 12 mm



technical data

general data

manufacturer Myutron

mechanical data

lens mount M58-mount

dimensions 70 mm × 115 mm

max. outer diameter 70 mm (without knurled screws)
74 mm (with knurled screws)

max. length (excl. thread) 111 mm

weight ≤ 494 g

filter thread M 67,0 × 0,75

lens data

lens resolution 48 MP

focal length 50 mm

focal range ≥ 50 mm

format 44 mm

aperture F2.8-22

aperture control manual

M.O.D. 0,19 m

environmental conditions

operating temperature 0 ... +40 °C