

## ZVL-FL-BC5024-9M

Article number: 11154327

### overview

- Ricoh Imaging lens
- 50 mm
- F 2,4-22
- format 1,1"
- M.O.D. 0,2 m
- locating screw for aperture and focus
- C-mount



### technical data

#### general data

manufacturer Ricoh Imaging

#### mechanical data

lens mount C-mount

dimensions 42 mm × 69,0 mm

max. outer diameter 42 mm (without knurled screws)  
52 mm (with knurled screws)

max. length (excl. thread) 69 mm

weight ≤ 166 g

filter thread M 40,0 × 0,5

#### lens data

lens resolution 12 MP

focal length 50 mm

focal range ≥ 50 mm

format 1,1"

aperture F2,4-22

aperture control manual

M.O.D. 0,2 m