

ZVL-FL-CC0814A-2M

Article number: 11150223

overview

- Ricoh Imaging lens
- 8 mm
- F 1,4-16
- format 2/3"
- M.O.D. 0,1 m
- locating screw for aperture and focus
- C-mount



technical data

general data

manufacturer Ricoh Imaging

mechanical data

lens mount C-mount
 dimensions 42 mm × 36,7 mm
 max. outer diameter 42 mm (without knurled screws)
 45 mm (with knurled screws)
 max. length (excl. thread) 36,7 mm
 weight ≤ 76 g

mechanical data

filter thread M 40,5 × 0,5

lens data

lens resolution 2 MP
 focal length 8 mm
 format 2/3"
 aperture F1,4-16
 aperture control manual
 M.O.D. 0,1 m