

ZVL-FL-CC1614A-2M

Article number: 11150228

overview

- Ricoh Imaging lens
- 16 mm
- F 1,4-16
- format 2/3"
- M.O.D. 0,1 m
- locating screw for aperture and focus
- C-mount



technical data

general data

manufacturer Ricoh Imaging

mechanical data

lens mount C-mount

dimensions 29,5 mm × 32,2 mm

max. outer diameter 29,5 mm (without knurled screws)
39,5 mm (with knurled screws)

max. length (excl. thread) 32,2 mm

weight ≤ 54 g

filter thread M 27,0 × 0,5

lens data

lens resolution 2 MP

focal length 16 mm

focal range ≥ 12 mm ... < 25 mm

format 2/3"

aperture F1,4-16

aperture control manual

M.O.D. 0,1 m