

## ZVL-FL-CC2514-2M

Article number: 11002222

### overview

- Ricoh Imaging lens
- 25 mm
- F 1,4-16
- format 2/3"
- M.O.D. 0,25 m
- locating screw for aperture and focus
- C-mount



### technical data

#### general data

manufacturer Ricoh Imaging

#### mechanical data

lens mount C-mount

dimensions 29,5 mm × 32,0 mm

max. outer diameter 29,5 mm (without knurled screws)  
39,5 mm (with knurled screws)

max. length (excl. thread) 32 mm

weight ≤ 55 g

filter thread M 27,0 × 0,5

#### lens data

lens resolution 2 MP

focal length 25 mm

#### lens data

focal range ≥ 25 mm ... < 50 mm

format 2/3"

aperture F1,4-16

aperture control manual

M.O.D. 0,25 m

horizontal angle of view 20 °

vertical angle of view 15,1 °

diagonal angle of view 24,9 °

at image format 8,8 × 6,6 mm

#### environmental conditions

operating temperature -20 ... +50 °C