

ZVL-FL-CC3516-2M

Article number: 11003417

overview

- Ricoh Imaging lens
- 35 mm
- F 1,6-16
- format 2/3"
- M.O.D. 0,35 m
- locating screw for aperture and focus
- C-mount



technical data

general data

manufacturer Ricoh Imaging

mechanical data

lens mount C-mount

dimensions 29,5 mm × 35,4 mm

max. outer diameter 29,5 mm (without knurled screws)
39,5 mm (with knurled screws)

max. length (excl. thread) 35,4 mm

weight ≤ 64 g

filter thread M 27,0 × 0,5

lens data

lens resolution 2 MP

focal length 35 mm

lens data

focal range ≥ 25 mm ... < 50 mm

format 2/3"

aperture F1,6-16

aperture control manual

M.O.D. 0,45 m

horizontal angle of view 14,8 °

vertical angle of view 11,1 °

diagonal angle of view 18,4 °

at image format 8,8 × 6,6 mm

environmental conditions

operating temperature -20 ... +50 °C