

ZVL-FL-CC5024A-2M

Article number: 11150230

overview

- Ricoh Imaging lens
- 50 mm
- F 2,4-22
- format 2/3"
- M.O.D. 0,3 m
- locating screw for aperture and focus
- C-mount



technical data

general data

manufacturer Ricoh Imaging

mechanical data

lens mount C-mount
 dimensions 32 mm × 46,5 mm
 max. outer diameter 32 mm (without knurled screws)
 42 mm (with knurled screws)
 max. length (excl. thread) 46,5 mm
 weight ≤ 66 g

mechanical data

filter thread M 30,0 × 0,5

lens data

lens resolution 2 MP
 focal length 50 mm
 format 2/3"
 aperture F2,4-22
 aperture control manual
 M.O.D. 0,3 m