

ZVL-FL-CC7528-2M

Article number: 11003041

overview

- Ricoh Imaging lens
- 75 mm
- F 2,8 32
- format 2/3"
- M.O.D. 0,7 m
- locating screw for aperture and focus
- C-mount



technical data

general data

manufacturer Ricoh Imaging

mechanical data

lens mount C-mount

dimensions 34 mm × 59,6 mm

max. outer diameter 34 mm (without knurled screws)
44 mm (with knurled screws)

max. length (excl. thread) 59,6 mm

weight ≤ 125 g

filter thread M 30,5 × 0,5

lens data

lens resolution 2 MP

focal length 75 mm

lens data

focal range ≥ 50 mm

format 2/3"

aperture F2,8-32

aperture control manual

M.O.D. 0,7 m

horizontal angle of view 6,9 °

vertical angle of view 5,2 °

diagonal angle of view 8,6 °

at image format 8,8 × 6,6 mm

environmental conditions

operating temperature -20 ... +50 °C