

ZVL-FL-HC0614-2M

Article number: 11008992

overview

- Ricoh Imaging lens
- 6 mm
- F 1,4-16
- format 1/2"
- M.O.D. 0,1 m
- locating screw for aperture and focus
- C-mount



technical data

general data

manufacturer Ricoh Imaging

mechanical data

lens mount C-mount

dimensions 32 mm × 37,5 mm

max. outer diameter 32,6 mm (without knurled screws)
42,5 mm (with knurled screws)

max. length (excl. thread) 37,5 mm

weight ≤ 65 g

filter thread M 30,5 × 0,5

lens data

lens resolution 2 MP

focal length 6 mm

focal range < 12 mm

format 1/2"

aperture F1,4-16

aperture control manual

M.O.D. 0,1 m

horizontal angle of view 57,4 °

environmental conditions

operating temperature -20 ... +50 °C