

overview

- Ricoh Imaging lens
- 50 mm
- F 2,8-22
- format 45 mm
- M.O.D. 0,25 m
- locating screw for aperture and focus
- F-mount



technical data

general data

manufacturer Ricoh Imaging

mechanical data

lens mount F-Mount

dimensions 72 mm × 56,8 mm

max. outer diameter 72 mm (without knurled screws)
82 mm (with knurled screws)

max. length (excl. thread) 56,8 mm

weight ≤ 370 g

filter thread M 62,0 × 0,75

lens data

lens resolution 48 MP

focal length 50 mm

focal range ≥ 50 mm

format 45 mm

aperture F2,8-22

aperture control manual

M.O.D. 0,25 m