

ZVL-N118F0818IRCSR3

Article number: 11166844

overview

- Kowa lens
- 8 mm
- F 1,4-16
- format 1"
- M.O.D. 0,2 m
- CS-mount



technical data

general data

manufacturer Evetar

mechanical data

lens mount CS-mount

dimensions 30 mm × 21 mm

max. outer diameter 30 mm (without knurled screws)
40 mm (with knurled screws)

max. length (excl. thread) 21 mm

lens data

lens resolution 3 MP

focal length 7,8 mm

focal range < 12 mm

format 1/1.8"

aperture F1:1,8

aperture control manual

M.O.D. 0,2 m