

ZVL-M118F1218IRCS

Article number: 11166843

overview

- Kowa lens
- 12 mm
- F 2,0-16
- format 4/3"
- M.O.D. 0,3 m
- CS-mount



technical data

general data

manufacturer Evetar

mechanical data

lens mount CS-mount

dimensions 30 mm × 15,3 mm

max. outer diameter 30 mm (without knurled screws)
40 mm (with knurled screws)

max. length (excl. thread) 15,3 mm

lens data

lens resolution 3 MP

focal length 12 mm

focal range $\geq 12 \text{ mm} \dots < 25 \text{ mm}$

format 1/1.8"

aperture F1:1,8

aperture control manual

M.O.D. 0,3 m