

overview

- dual port GigE PCIe x4 interface board with PoE support
- GigE cables 3,0 m (2 pieces)
- trigger/flash cable, 5,0 m
- power supply kit for LX, PX and VCXG cameras
- Mounting Adapter Type B (Tripod)
- Software (WINDOWS, LINUX, LINUX ARM) via Download
- camera not included



technical data

fixing

article number	11003060
name	Mounting Adapter Type B (Tripod)
features	• easy camera mounting • robust anodized surface • stable lightweight metal design (aluminium, 17g) • UNC 1/4" - 20 thread for mounting (tripod thread)

cable

article number	10170048
name	2x cable GigE RJ45/RJ45, 3,0 m
features	• GigE cable • RJ45/RJ45 • CAT7 • length 3,0 m

process interface cable

article number	11004523
name	cable 8 wires, 5,0 m (ESG 32FH0500)
features	• cable • M8 female connector • 8-pin • open wires at one side • cable carrier compatible • length 5,0 m

interface card

article number	11168453
name	PCI-1672PC Dual PoE (ZVA-PCIe-1672PC)
features	• 2 port GigE to PCI Express host adapter • RJ45 connector • chipset: Intel® I350-AM2 • Power over Ethernet, IEEE 802.3af compliant, support class 0, 1, 2, 3, and 4, provides up to 15,4 Watt • tested Jumbo Frames: 9 kByte • Note: 4 lane PCI Express connector required

power supply

article number	11122415
name	Power Supply Kit LX PX VCXG int.
features	• power supply 12V/2,0A international with adapters for EU, US, UK, AU, KR and power supply and process interface adapter cable for LX, PX and VCXG cameras • length 5,0 m