

overview

- GigE PCIe interface board
- Gigabit Ethernet cable 3,0 m
- process interface cable 5,0 m
- Power Supply Kit *VisiLine* int.
- Mounting Adapter Type A (Front)
- Mounting Adapter Type B (Tripod)
- Software (WINDOWS, LINUX, LINUX ARM) via Download
- camera not included



technical data

fixing

article number	11002638
name	Mounting Adapter Type A (Front)
features	<ul style="list-style-type: none"> • easy camera mounting • robust anodized surface • stable lightweight metal design (aluminium, 17g)
article number	11003060
name	Mounting Adapter Type B (Tripod)
features	<ul style="list-style-type: none"> • easy camera mounting • robust anodized surface • stable lightweight metal design (aluminium, 17g) • UNC 1/4"- 20 thread for mounting (tripod thread)

cable

article number	10170048
name	cable GigE RJ45/RJ45, 3,0 m
features	<ul style="list-style-type: none"> • GigE cable • RJ45/RJ45 • CAT7 • length 3,0 m

process interface cable

article number	11105264
name	shielded cable 3 wires, 5,0 m (Z-KSG 32SH0500G)

process interface cable

features	<ul style="list-style-type: none"> • shielded cable • M8 male connector • 3-pin • open wires at one side • cable carrier compatible • length 5,0 m
----------	--

interface card

article number	11137188
name	PCIe Ethernet Server Adapter I210-T1 (ZVA-PCIe_Intel_Eth_Server_Adptr_I1210-T1)
features	<ul style="list-style-type: none"> • 1 port GigE to PCI Express host adapter • RJ45 connector • chipset: Intel® i210 Gigabit Controller • tested Jumbo Frames: 9 kByte • 1 lane interface

power supply

article number	11113400
name	Power Supply Kit <i>VisiLine</i> ® int.
features	<ul style="list-style-type: none"> • power supply 12V/2,0A international with adapters for EU, US, UK, AU, KR and power supply and process interface adapter cable for <i>VisiLine</i>® cameras • length 5,0 m