

overview

- USB 3.0 interface cable
- screw lock Micro-B connector to type A (optional screw lock) connector, both connectors with die-cast housing
- length 5,0 m
- coaxial cable



technical data

electrical data

number of poles	9
connectors	USB 3.0 Micro-B connector, screw lock, die-cast housing USB 3.0 type A connector, optional screw lock, die-cast housing

mechanical data

bending radius static	125 mm
-----------------------	--------

mechanical data

use in cable carriers	no
cable length [m]	5 m
weight	≤ 380 g
material	FLEX PVC (lead-free)

interface

data interface	USB 3.0
----------------	---------