

Obj Xenoplan 1,4/17-0903

Article number: 10170041

overview

- Schneider Kreuznach lens
- 17 mm
- F 1,4-11
- format 2/3"
- M.O.D. 0,16 m
- C-mount



technical data

general data

manufacturer Schneider Kreuznach

mechanical data

lens mount C-mount
 dimensions 34 mm × 37,8 mm
 max. outer diameter 34 mm (without knurled screws)
 44 mm (with knurled screws)
 max. length (excl. thread) 33,4 mm
 weight ≤ 85 g
 filter thread M 30,5 × 0,5

lens data

lens resolution 5 MP
 focal length 17 mm
 focal range ≥ 12 mm ... < 25 mm
 format 2/3"
 aperture F1,4-11
 aperture control manual
 M.O.D. 0,16 m

environmental conditions

storage temperature -25 ... +70 °C