

FLDR-i90B-SR24

Article number: 11154321

overview

- flashable LED ring light
- red (626 nm)
- 24 V
- voltage-driven (equipped with integrated pre-resistor)
- cable length: 0,3 m
- diameter: 94 mm



technical data

general data

manufacturer Falcon Illumination MV GmbH & Co.KG

illumination data

color red (626 nm)

illumination characteristic direct

illumination mode flashable

electrical data

connectors M8/4-pin male connector

illumination control voltage-driven (equipped with integrated pre-resistor)

current 0,6 A

current at flash mode $\leq 1,5$ A

voltage at flash mode ≤ 48 V DC

duty cycle 0-10%

electrical data

maximum flash duration 10 ms

mechanical data

construction design ring light

dimensions $\varnothing 93,5$ mm

height 24,6 mm

dimensions luminous area $\varnothing 30$ mm

cable length [m] 0,3 m

weight ≤ 200 g

material aluminum

environmental conditions

operating temperature 0 ... +35 °C

humidity 20% - 85%

protection class IP 30

dimension drawing

