

Obj LINOS MeVis C 50mm/f1,8

Article number: 11051406

overview

- Linos lens
- 50 mm
- F 1,8-16
- format 1"
- M.O.D. 0,67 m
- C-mount
- Phase-Out starting 08/20, alternative via sales



technical data

general data

manufacturer Linos

mechanical data

lens mount C-mount

dimensions 42 mm × 67,5 mm

max. outer diameter 42 mm (without knurled screws)
52 mm (with knurled screws)

max. length (excl. thread) 67,5 mm

weight ≤ 240 g

filter thread M 35,5 × 0,5

lens data

lens resolution 20 MP

focal length 50 mm

focal range ≥ 50 mm

format 1"

aperture F1,8-16

aperture control manual

M.O.D. 0,67 m