

ZVL-E3146B-R1

Article number: 11701909

overview

- Evetar lens
- 5,4 mm
- F 2,8
- format 1/2,3"
- M.O.D. 0,3 m
- IR Cut Filter
- S-mount



technical data

general data

manufacturer Evetar

mechanical data

lens mount S-mount

dimensions 13,5 mm × 18,74 mm

max. length (excl. thread) 4,3 mm

weight ≤ 6 g

lens data

lens resolution 10 MP

focal length 5,4 mm

focal range < 12 mm

lens data

format 1/2.3"

aperture F2,8

aperture control fix

M.O.D. 0,3 m

horizontal angle of view 60,5 °

vertical angle of view 32,2 °

diagonal angle of view 72,4 °

at image format 6,2 × 3,1 mm

environmental conditions

operating temperature -20 ... +50 °C