

Obj Cinegon 1,4/8-0902

Article number: 11035932

overview

- Schneider Kreuznach lens
- 8 mm
- F 1.4-8
- format 2/3"
- M.O.D. 0.072 m
- C-mount



technical data

general data

manufacturer Schneider Kreuznach

mechanical data

lens mount C-mount

dimensions 34 mm × 37,5 mm

max. outer diameter 34 mm (without knurled screws)
50 mm (with knurled screws)

max. length (excl. thread) 32,4 mm

weight ≤ 134 g

filter thread M 30,5 × 0,5

lens data

lens resolution 5 MP

focal length 8 mm

focal range < 12 mm

format 2/3"

aperture F1,4-8

aperture control manual

M.O.D. 0,072 m

environmental conditions

storage temperature -25 ... +70 °C