

Overview

- USB 3.0 interface cable
- screw lock Micro-B connector to type A (optional screw lock) connector, both connectors with die-cast housing
- length 5.0 m



technical data

electrical data

number of poles	9
connectors	USB 3.0 Micro-B connector, screw lock, die-cast housing USB 3.0 type A connector, optional screw lock, die-cast housing

mechanical data

smallest bending radius static	62 mm
use in cable carriers	no

mechanical data

cable length [m]	5 m
weight	≤ 250 g
material	PVC

interface

data interface	USB 3.0
----------------	---------

environmental conditions

conformity	RoHS CE
------------	------------