

## ZVL-E3196B

Article number: 11701908

### Overview

- Evetar lens
- 12 mm
- F 2,0
- format 1/1,8"
- M.O.D. 0,3 m
- S-mount



### Technical data

#### General data

Manufacturer Evetar

#### Mechanical data

Lens mount S-mount

Dimensions 15 mm × 19,2 mm

Max. length (excl. thread) 6 mm

Weight ≤ 6 g

#### Lens data

Lens resolution 6 MP

Focal length 12 mm

Focal range ≥ 12 mm ... < 25 mm

#### Lens data

Format 1/1.8"

Aperture F2,0

Aperture control fix

M.O.D. 0,3 m

Horizontal angle of view 33,6 °

Vertical angle of view 25,3 °

Diagonal angle of view 41,3 °

At image format 7,18 × 5,38 mm

#### Environmental conditions

Operating temperature -20 ... +50 °C