

产品一览

- SmartReflect - Safe barrier principle without reflector
- Baumer PinPoint LED: Small, homogeneous light spot with sharp edges
- Long-term stable detection of transparent objects thanks to compensation of environmental influences
- qTeach - tamper-proof, simple teach-in with ferromagnetic tool
- Quick mounting by means of M3 threaded bushes made of stainless steel




图片与实际产品相似




技术数据

基本参数		电气参数	
类型	光栅	压降 Vd	< 2 VDC
版本	透明物体检测	输出功能	亮通 / 暗通 功能
光源	脉冲PinPoint LED	输出电路	NPN 互补
背景位置 Sde	25 ... 180 mm	输出电流	< 50 mA
感应范围 Sa	90% ... 85% Sde	短路保护	是
最低信号衰减强度	10 %	反极性保护	是
调节/镜头受污指示灯	闪烁输出指示灯	机械参数	
上电指示灯	绿色LED	宽度 / 直径	8 mm
输出指示灯	黄色LED	高度 / 长度	25,1 mm
感应距离调节	qTeach	深度	15,8 mm
波长	644 nm	类型	矩形
交互影响抑制	是	Mechanical mounting	带M3螺纹的袖子(不锈钢)
光束类型	点	外壳材质	塑料 (ASA 、 PMMA)
光轴校准	< 1,5°	前端光学元件	PMMA
电气参数		连接方式	电缆 · 4针 · 2 m
电源电压范围 +Vs	10 ... 30 VDC	Cable characteristics	PVC / PVC 4 x 0,08 mm ²
最大电流消耗 (无负载)	40 mA (@ 10 VDC)	环境条件	
典型电流消耗	16 mA (@ 24 VDC)	防护等级	IP 67
		工作温度	-25 ... +50 °C

尺寸图



接线图



典型光束特性

