

Accessories

Connectors and cables

Female connector M23, 12-pin, straight, version 1



Features

- Female connector M23 with screwable nut
- With or without cable (shielded) in different lengths
- Cable version: shield is placed onto the connector housing

Part number

10107687	Female connector M23, 12-pin, straight, without cable
10118532	Female connector M23, 12-pin, straight, 5 m cable
10130367	Female connector M23, 12-pin, straight, 2 m cable

Suitable for

BDH, BDH - *HighRes*, BDT, BDT - *HighRes*, BHF, BHG, BHT, BHW, BRID, BRIH, BRIV 58K, BRIV 58S

Technical data

Bending radius	10 x cable diameter
Outer diameter	5.5 ±0.2 mm
Operating temperature	-40...+90 °C (fixed cable)

Terminal assignment

Connector	Core colour
Pin 1	red
Pin 2	brown
Pin 3	pink
Pin 4	grey
Pin 5	yellow
Pin 6	blue
Pin 7	–
Pin 8	green
Pin 9	–
Pin 10	white
Pin 11-12	–

Assembly drawing

