

0.2" (5.2)

plastic clip

0.78" (19.8)



3x hex socket  
head cap screw  
N 8-32 UNC x 1/4

1" (25.4)

bore  
diameter  
for 1/4"  
(6.35)

flexible  
torque  
support

d

1.18" (30)

2.81" (71.5)

4.49" (114)

$\varnothing 2.87"$  ( $\varnothing 73$ )

$\varnothing 2.44"$  ( $\varnothing 62$ )

$\varnothing 2"$  ( $\varnothing 50.8$ )

