

ZVL-FL-CC0614A-2M

Article number: 11150221

Overview

- Ricoh Imaging lens
- 6 mm
- F 1,4-16
- format 1/2"
- M.O.D. 0,1 m
- locating screw for aperture and focus
- C-mount



Technical data

General data

Manufacturer Ricoh Imaging

Mechanical data

Lens mount C-mount

Dimensions 48 mm × 59,9 mm

Max. outer diameter 48 mm (without knurled screws)
50 mm (with knurled screws)

Max. length (excl. thread) 59.9 mm

Weight ≤ 149 g

Lens data

Lens resolution 2 MP

Focal length 6 mm

Format 2/3"

Aperture F1,4-16

Aperture control Manual

M.O.D. 0.1 m