

ZVL-FL-CC1614A-VG

Article number: 11009196

Overview

- Ricoh Imaging lens
- 16 mm
- F 1,4-22
- format 2/3"
- M.O.D. 0,3 m
- locating screw for aperture and focus
- compact size (Ø 30,0 mm)
- C-mount



Technical data

General data

Manufacturer Ricoh Imaging

Mechanical data

Lens mount C-mount

Dimensions 30 mm × 33 mm

Max. outer diameter 30 mm (without knurled screws)
40 mm (with knurled screws)

Max. length (excl. thread) 33 mm

Weight ≤ 58 g

Filter thread M 27,0 × 0,5

Lens data

Lens resolution 0.3 MP

Focal length 16 mm

Lens data

Focal range ≥ 12 mm ... < 25 mm

Format 2/3"

Aperture F1,4-22

Aperture control Manual

M.O.D. 0.3 m

Horizontal angle of view 30.7 °

Vertical angle of view 23.2 °

Diagonal angle of view 38.2 °

At image format 8,8 × 6,6 mm

Environmental conditions

Operating temperature -20 ... +50 °C